

## Four-sided Universal Applicator



This four-sided applicator, also known as a baker-type applicator combines 4 gaps sizes in one unit. The cylindrical shape design provides excellent results particularly on firm substrates and smooth surfaces. By simply rotating through 90° angles, the next gap size is placed onto the test surface. Relevant Standard: ASTM D823 Section 25

Wet Film Width: 80mm

Total Length: 100mm

Product Code	Depth
T01-700068	5µm / 10µm / 15µm / 20µm
T01-700069	25µm / 50µm / 75µm / 100µm
T01-700070	50µm / 100µm / 150µm / 200µm
T01-700071	30µm / 60µm / 90µm / 120µm
T01-700072	100µm / 200µm / 300µm / 400µm
T01-700073	50µm / 75µm / 100µm / 150µm
T01-700074	100µm / 150µm / 200µm / 250µm
T01-700075	250µm / 500µm / 750µm / 1000µm



Customised applicators also available -please contact us with your requirements

## Method

1. Before each use check the working surfaces of the applicator for any irregularities and damage.
2. Fix a clean substrate on a flat and horizontal base (e.g., vacuum table).
3. At one end of the substrate, spread sufficient product over a width slightly less than the internal width of the applicator.
4. Place the applicator onto the substrate behind the product.



5. Spread the film by moving the applicator towards the opposite end of the substrate at a constant speed.
6. Lift the applicator from the substrate taking care to catch any product dripping from the applicator. After the test, clean your film applicator thoroughly



### NOTE:

Do not use aggressive solvents or wire brushes, metal scrapers, metal files or other abrasive tools for cleaning. Clean the applicator using a suitable solvent only.