

## Multifunction High Speed Disperser



Product Code T01-20656

With a brushless motor for smooth and quiet operation, the Multifunction High Speed Disperser is operated by the intuitive touch screen menu. The built-in infrared probe allows for monitoring of samples throughout testing without disturbance.

It has a timer function that ensures testing is stopped when the set time is reached. An emergency stop button ensures that the machine can be quickly and safely stopped if required

Samples are held in place securely by the integral clamp which is adjusted easily by the manual adjuster

A wide variety of blades are available as separate accessories along with containers designed for use with the disperser. (Please see next page for ordering information)

Power	1000W (Brushless DC motor)
Adjustable Working Speed	200~6,000r/min
Lift Height	260 mm
Overall Dimensions	450mm×450mm×700mm
Net Weight	40KG

Supplied with dispersing blades: one each of  $\Phi$ 50mm and  $\Phi$ 80mm

Ascott Analytical Equipment Limited

6-8 Gerard, Lichfield Road Industrial Estate, Tamworth, Staffordshire, B79 7UW, Great Britain

T +44 (0) 1827 318040 F +44 (0) 1827 318049 E info@ascottshop.com W www.ascottshop.com

## Multifunction High Speed Disperser

### Accessories

Product Code	Description
T01-20657	Dispersing Blade – 35mm
T01-20658	Dispersing Blade – 50mm
T01-20659	Dispersing Blade – 60mm
T01-20660	Dispersing Blade – 80mm
T01-20661	Dispersing Blade – 100mm
T01-20662	Dispersing Blade – 120mm
T01-20663	Dispersing Blade – 150mm
T01-20664	Dispersing Blade – 200mm
T01-20665	Dispersing Blade with 4 apertures for low viscosity samples – 50mm
T01-20666	Dispersing Blade with 4 apertures for low viscosity samples – 60mm
T01-20667	Heavy Duty Dispersing Blade for high viscosity samples – 50mm
T01-20668	Heavy Duty Dispersing Blade for high viscosity samples – 60mm
T01-20669	Dispersing Container 0.3 L Single walled
T01-20670	Dispersing Container 0.5 L Double walled
T01-20671	Dispersing Container 1.25 L Double walled
T01-20672	Dispersing Container 3 L Double walled
T01-20673	Dispersing Container 5 L Double walled
T01-20674	Dispersing Container 10 L Double walled
T01-20675	Dispersing Container 20 L Double walled



Ascott Analytical Equipment Limited

6-8 Gerard, Lichfield Road Industrial Estate, Tamworth, Staffordshire, B79 7UW, Great Britain

T +44 (0) 1827 318040 F +44 (0) 1827 318049 E info@ascottshop.com W www.ascottshop.com